

**Polarization Maintaining Components** 

## **Key Features**

- Low Insertion Loss
- High Extinction Ratio
- Compact Design
- Wide Operating Wavelength
- High Reliability and Stability


# **Applications**

- PM Circulators
- PM WDM
- PM Coupler
- Signal Processing

## 1310nm Polarization Maintaining Single Fiber Collimator

The PM Fiber Collimator is the basic element for in-line PM fiber optics components, such as PM isolator and PM DWDM. It has high extinction ratio, low insertion and high return loss. The unique processing and high-quality AR coating also enable this collimator to handle high power.

If you do not see a standard PM Fiber Collimator that meets your needs, we welcome the opportunity to review your desired specification and quote a custom PM Fiber Collimator. Requests for custom fiber pigtails, different wavelengths and handling power of operation or other specific needs will be readily addressed.



# For more Info

#### Please contact us at:

Tel: +86-755-23736280

Fax: +86-755-26746512


E-mail: sales@dkphotonics.com

https://www.dkphotonics.com

#### Add.:

4F, Bldg. 18, Qinghu Industrial Park, Dahe Road, Longhua Dis., Shenzhen, China 518109

# Package Dimension:



\*Due to ongoing design improvements, the package size is subject to change. Please contact DK Photonics for confirmation if you have special requirements.





# 1310nm Polarization Maintaining Single Fiber Collimator

### **Performance Specifications**

Parameter	Unit	V	Values			
Туре	-	Standard	Long working distance			
Operating wavelength ( $\lambda c$ )	nm		1310			
Operating wavelength range	nm		±30			
Max. Working Distance	mm	20	50~100(C-lens)			
Max. Insertion Loss (λc @1310nm)	dB	0.20	0.30			
Waist Beam Diameter	mm	~0.35	~0.45			
Min. Extinction Ratio	dB		23			
Min. Return Loss	dB		55			
Fiber Type	-	PM1300->	PM1300-XP Panda fiber			
Max. Power Handling	W	0.5, 1	0.5, 1, 3, 5, 10			
Operating temperature	°C	-{	-5~+70			
Storage temperature	°C	-4	-40~+85			
Dimension 1.8(OD lens)	mm	Φ3.2x10(Metal holder)	Φ3.2x10(Metal holder) or Φ2.78x9.0 (Glass tube)			


1. The specifications are w/o connector. Other lens sizes can also be customized according to requirements.

2. For devices with connectors, IL will be 0.3dB higher, RL will be 5dB lower and ER will be 2dB lower. The default connector key is aligned to slow axis. Power transmits through the connector less than 2W.

3. Waist Beam Diameter is measured at the alignment wavelength at 1/2 working distance.

4. When purchasing the collimator, please inform us whether it is used alone or in pairing. If paired, we will pack and ship the paired ones together.

5. For G-lens, Working Distance <20mm



#### Order information P/N: PMCOLL-S-2-3-4-5-6-7-8(S: single fiber)

When you inquire, please provide the correct P/N number according to our ordering information, and attach the appropriate description would be better. If need any connector, we do not recommend choosing a 250µm bare fiber pigtail.

1	0	3	4	6	6	0	8
Wave- length	Working Distance	Power Handling	Lens Type	Pigtails Diameter	Fiber Length	Connectors	Dimension
13:1310nm	0:<0mm	L:<0.5W	C: C-lens	25:250µm bare	10:1.0m	00: None	3.2x10
XX: Others	5:5mm 10:10mm	1:1W 3:3W	G: G-lens	fiber 90:900µm Loose	13:1.3m 15:1.5m	FP: FC/PC FA: FC/ APC	2.78x9
	10.101111	5:5W		Fiber	20:2.0m	XX: Others	
				XX: Others	XX: Others		

Part Number Example: PMCOLL-S-13-5-L-C-25-10-00-2.78X9

**Description:** 1310nm Polarization Maintaining Single Fiber Collimator, 5mm working distance ,0.5W handling power, C lens, PM1300 Panda fiber, bare fiber, 1.0m fiber length, and no connector, package dimension:2.78x9mm. Used alone.

## **Ordering Information for Custom Parts**

If you need to customize other specifications, please provide detailed description for your requirement.